



ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE









PCB LAYOUT

SPECIFICATION:
- Current Rating: 3AMP
- Temperature Range: −40℃to+105℃
- Contact Resistance: 20mΩ Max
- Insulation Resistance: 1000MΩ Min
- Withstanding Voltage: AC 1000V

Material:
- Insulator: Polyester (UL94V−0)
- Standard: PA9T
- Contact: Brass
- Plating: Au over Ni

COSTOMER DRAWING			深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
DRAWING			TITLE	排母 PIN距2.54 塑高8.5 单排2PIN弯针	REV. A
CHECKED			PART NO.	LAIL-PM2.54-2P-W	UNITS mm
APPROVED			DWG. NO.		Projection
TOLERANCES ARE					
30-150	±0.35	ANGLE			
10-30	±0.2				
5-10	±0.15	±3°			
0-5	±0.1				