

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
G	86

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	ECR-13-000998	11FEB2013	PK	HS





1. TIN PL .000150 MIN THK PER ASTM B 545
2. PART NO: 324466; .243 LB.
   PART NO: 1-324466-0; .243 LB.
   PART NO: 2-324466-1; .243 LB.
   PART NO: 2-324466-2; .269 LB.
3. RED COLOR CODE
4. CLEANED, UNPLATED
5. .045 MAX BURR ALLOWED INSIDE THE WIRE BARREL ID IN AREA OF SIGHT HOLE.

"C"	"B"	"A"	FINISH	WIRE RANGE	MATERIAL	PART No
1.07	1.32	2.64	1	450-550 MCM	COPPER ASTM-B-75 ANNEALED	2-324466-2
OBSOLETE			1 3			~~2-324466-1~~
1.07	1.07	2.41	4			1-324466-0
			1			324466

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±–
1 PLC ±–
2 PLC ±–
3 PLC ±–
4 PLC ±–
ANGLES ±–

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN DK SCHRUM 4/24/89
CHK MS FEHER 4/24/89
APVD WJ VOCKROTH 11/8/89
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT 2

TE Connectivity

NAME: SPLICE, BUTT, AMPOWER WIRE SIZE: 500 MCM

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-324466	–

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV R

1470-19 (3/11)