



End plate, Width: 2 mm, Colour: Blue

RAL: Ähnlich 5005

Business data

Article number	3704.5
Article name	ZAP 4/3A BU
GTIN (EAN)	4044211060190
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	2.4 g
Weight per piece (including packaging)	2.5 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	3704.2
Product description	End plate

Technical data

Dimensions

Length	78.5 mm
Width	2 mm
Height	33.9 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

##INVERSE##CONTA-CONNECT



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm², Width: 6.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3526.2</u>	ZSL 4/3A GNYE	4044211151805	100 ST



Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm², Width: 6.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1723.2</u>	ZSL 4/3A Ex GNYE	4044211058708	100 ST



Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm², Width: 6.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1717.2</u>	ZRK 4/3A Ex BG	4044211058609	100



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm², Width: 6.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3516.2</u>	ZRK 4/3A BG	4044211151775	100