


© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-10-005637	23MAR2010	WS	RP
	B	REVISED PER ECO-19-012987	30AUG2019	AP	SY







1. MATERIAL:
   CONTACT - PHOS BRONZE
   HOUSING - LCP, UL 94V-0, COLOR - BLACK

2. FINISH:
   CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303-1; BASED ON TELECORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).


3. CONNECTOR MARKED WITH PART NUMBER, DATE CODE, 85 OHM, AND STANDARD IN APPROXIMATE AREA SHOWN.

4. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.

6. REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.

7. SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIAMATE AREA



RECOMMENDED PC BOARD
LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 6:1

1934937-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL 1

FINISH 2

DWN J.K.SHOBER 27MAY2008
CHK C.RITTER 27MAY2008
APVD C.RITTER 27MAY2008
PRODUCT SPEC 108-2303-1
APPLICATION SPEC 114-13243
WEIGHT -

TE Connectivity

NAME HEADER ASSEMBLY, OPEN ENDED, 5 PAIR, 10 COLUMN TinMan 85 OHM

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-1934937	

RESTRICTED CUSTOMER

SCALE 10:1 SHEET 1 OF 1 REV B