
Data Sheet

HUBER+SUHNER

Coaxial Cable Connector
25_TNC-50-2-1/133_N

Description

Straight panel cable jack, flange mount



Interface standards
IEC 60169-17_MIL-STD-348A/313_CECC 22200

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0193 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00048074
Catalogue drawing	DCA-00009017
Assembly instruction	DOC-0000179064

Ordering Information

Single package	25_TNC-50-2-1/133_NE

Additional Information

Suitable cables	RG_316_/U, RG_188_A/U, RG_174_/U

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.