

性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: $30\text{m}\Omega$ max


绝缘电阻: $500\text{M}\Omega$

工作温度: $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$

使用寿命: 5000次以上

塑件(材质): PA9T黑色, 耐高温 260°C

接触点(材质): 黄铜C2680, 触点镀金 $3\text{U}''$



RECOMMENDED PCB LAYOUT
TOP VIEW (.XX ± 0.05)

规格型号	DIM A	DIM B
HYCW-BF2P42519D-72	8.50	7.25
HYCW-BF3P42519D-115	12.75	11.5
HYCW-BF4P42519D-157	17.00	15.75
HYCW-BF5P42519D-200	21.25	20.00
HYCW-BF6P42519D-242	25.5	24.25



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30
X.XX ± 0.25
X.XXX ± 0.15

X' $\pm 2'$ X.X' $\pm 0.5'$

UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY:

陈一鸣

DATE:

2014-02-23

PART NAME:

4.25PH 1.9H 母座有柱

CHECKED BY:

马跃

DATE:

2014-02-23

PART NO.

SEE TABLE

MOLD NO.

APPROVED BY:

邱敏

DATE:

2014-02-23

DRAW NO:

HYC-2604141052

SHEET NO.

1 OF 1