Data sheet

28127.7 PVCF-KMP 038 10X23 WH

Wire and cable markers, Length: 38 mm, Width: 23 mm, Colour: White

RAL: 9010

Business data

Article number	28127.7
Article name	PVCF-KMP 038 10X23 WH
GTIN (EAN)	4044211212667
Packaging unit	400
Quantity unit	PC
Number of markers per card	8 ST
Weight per piece (not including packaging)	0.66 g
Weight per piece (including packaging)	0.66 g
Unit of weight	G
Customs number	39204910
Country of origin	IT
Prio-Article	28127.7
Product description	Cable and wire markers

Data sheet

28127.7 PVCF-KMP 038 10X23 WH

Technical data

Dimensions	
Length	38 mm
Length of labelling field	23 mm
Width	23 mm
Width of labelling field	10 mm
Connection data	
Outer diameter of insulation, min.	4.3 mm
Max. outer diameter of insulation	7 mm
Materials	
Marker material	PVC film
Flammability class UL 94	V-0
Working temperature, min.	-30 °C
Working temperature, max.	70 °C
Processing temperature, min.	10 °C
Processing temperature, max.	40 °C
Silicone-free	✓
Further technical data	
Software code	302
Environmental Product Compliance	
REACH Candidate Substance Note	No

Data sheet

28127.7 PVCF-KMP 038 10X23 WH

Media

Data sheet

28127.7 PVCF-KMP 038 10X23 WH

Accessories

Printer



Thermal transfer printer TTPCard including a power cord, USB cable, dust cover, black thermal transfer film (28010.4), three inlays: CCI-PC-SB 5x5 (28020.0), CCI-PC-CPM-10/BSTR (28027.0), CCI-PC/PVC/PVCF (28041.0), CONTASign PRO software in 16 languages (German, English, French, Italian, Dutch, Spanish, Portuguese, Czech, Polish, Bulgarian, Romanian, Slovenian, Turkish, Chinese, Japanese, Russian) for Windows versions 7, 8, 10. (available for download)

Article number	Article name	GTIN (EAN)	Packaging unit
28000.0	TTPCard Set	4044211207397	1 ST

Inlays

Printer inlay

Article number	Article name	GTIN (EAN)	Packaging unit
28041.0	CCI-PC/PVC/PVCF	4044211208097	1 ST