



Eaton 3.6WFLSJ160

Eaton Bussmann series medium voltage motor fuse, 3.6 kV, 160A, 50 kAIC, Non Indicating, fuse, Class back-up

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage motor fuse
CATALOG NUMBER	3.6WFLSJ160
UPC	051712834797
PRODUCT LENGTH/DEPTH	292 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	76 mm
PRODUCT WEIGHT	3160 g
COMPLIANCES	VDE 0670-4 DIN 43625
CERTIFICATIONS	IEC60282-1

USED WITH	A3354730 Nickel-plated copper fuse clip
AMPERAGE RATING	160 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	76 x 292 mm
BREAKING CAPACITY	50 A
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Motor protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	DIN
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
FUSE SHAPE	Cylindrical
WATT LOSSES	61 W
RESISTANCE	1.74 ohms
FUSE DIAMETER	76 mm
INTERRUPT RATING	50 kAIC
CONSTRUCTION SIZE	76 x 292 mm
PACKAGING TYPE	Standard
VOLTAGE RATING	3.6 kV
TYPE	fuse
APPLICATION	Motor protection
FUSE TYPE	WFLSJ

