
Unique Surface Probes

OMEGA™

Adaptor Sold Separately
TAS-K-3
TAS-E-3

All the probes in this series meet the Standard Limits of Error.



TAS adaptor

All models supplied with a molded SMP or SMPW subminiature male connector. TAS adapter sold separately.

Model No. 88203(*)
Model No. 98203(*)
with Swivel Head

For rotating, smooth metallic surfaces of 229 to 610 mm (9 to 24") in diameter. 90 m (300') per minute maximum surface velocity. Maximum surface temperature of 205°C (400°F).

Replacement elements not included, to purchase additional elements order ***Model No. 88203(*)-RE.***

Model No. 88201(*)
Model No. 98201(*)
with Swivel Head

A roller-surface probe, for use on moving or rotating, smooth surfaces with a velocity up to 61 m (200') per minute. Maximum surface temperature of 205°C (400°F).

Replacement elements not included, to purchase additional elements order ***Model No. 88201(*)-RE.***

Visit us online for dimensions.

**** Specify Calibration:***
K: *CHROMEGA™-ALOMEGA™*
E: *CHROMEGA™-Constantan*

Model No. 88202(*)
Model No. 98202(*)
with Swivel Head


A roller-surface probe, ideal for measuring outside wall temperatures of smooth plastic or steel piping. Can be used on moving or rotating surfaces of 559 to 1524 mm (22 to 60") in diameter, with 90 m (300') per minute maximum surface velocity. Maximum surface temperature of 205°C (400°F).

Replacement elements not included, to purchase additional elements order ***Model No. 88202(*)-RE.***


Ordering Example: 98201K, *style 98201 swivel head roller surface probe in Type K thermocouple.*




Unique Surface Probes Series 88000




88001




88002 88003




88006




88007




88008




88010




88011




88012




88016




88026




88101




88102




88103




88104



88105




88106




88107

Dimensions: mm (inches)


Unique Surface Probes Series 88000/98000




88108




98225 Swivel
88225




98201 Swivel
88201




98226 Swivel
88226




98202 Swivel
88202




98227 Swivel
88227




98203 Swivel
88203




88301




98220 Swivel
88220




88305




98221 Swivel
88221




88306




88222




88307



88223



88308




88224


Dimensions: mm (inches)

Dimensions: mm (inches)

Model 88009



Model 88014



Model 88013

