


TABLE 1

SUB ASSEMBLY PART NO.	NO.	PART NO.	MATERIAL	COLOR	QTY.
7282-1198 ETC.	①	SEE TABLE 2	△4 PBT	SEE TABLE 2	1
	②	7157-4051	△4 PBT	NATURAL △3	1

TABLE 2

	SUB ASSEMBLY PART NO.	PART NO.	COLOR
	7282-1198, △3	7182-1198	NATURAL
	7282-1198-10, △3	7182-1198-10	DARK GRAY
	7282-1198-30, △3	7182-1198-30	BLACK
	7282-1198-40, △3	7182-1198-40	LIGHT GRAY
	7282-1198-50, △3	7182-1198-50	ORANGE
△2	7282-1198-60, △3	7182-1198-60	GREEN
△1	7282-1198-80, △3	7182-1198-80	BROWN
	7282-1198-90, △3	7182-1198-90	BLUE

注 記

1) 嵌合相手品番 : 7283-1198 ETC.

2) 適用端子品番 : 090Ⅱ 7114-4020 ETC.
187 7114-4030 ETC.

NOTES

1) MATING PART NO.: 7283-1198 ETC.

2) APPLICABLE TERMINAL NO. : 090Ⅱ 7114-4020 ETC.
187 7114-4030 ETC.

LET	DATE	REVISION RECORD	NO.	CHKD
△4	97.12.11	CHANGED MATERIAL	C97-N746	H.K
△3	96.07.11	CHANGED MATERIAL & CHANGED FORM, △3	C96-M145	H.K
△2	90.02.13	ADDED PART NO.	C90-L186	K.M
△1	89.09.07	ADDED PART NO.	C89-L961	M.H
	88.12.24	NEW	C89-L038	K.J

GENERAL TOLERANCE

	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15

SPECIFIED

MASS ...g

ISSUE MARK

CUSTOMER

CUSTOMER PART NO. | CUSTOMER DWG NO.

OFFICE | TRIAL PART NO.

VENDOR

VENDOR NO.

DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	88.12.24	mm	2/1	3

APPROVED	CHECKED	CHECKED	DESIGN	DRAWN
加藤	山梨	三輪	Y.OHTA	SERISAWA 杉山
97.12.23	97.12.23	97.12.18	87.10.09	97.12.11

MATL. SPEC. SEE TABLE 1 | TREAT. & FIN.

NAME 090Ⅱ 18P+187 1P HYBRID
CONNECTOR SUB ASSEMBLY MALE

PART NO. 7282-1198 ETC.
CH. CODE

DWG NO. 7282-1198: R | SET DWG NO.

YAZAKI CORPORATION