








Directive 2002/95/EC „RoHS" Compliant

NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
   PLATING: GOLD FLASH over NICKEL
   SOLDER CUP ACCEPTS CABLE AWG 20
4. HIGH POWER CONTACTS 20A: COPPER ALLOY
   PLATING MATING AREA: GOLD FLASH over NICKEL
   PLATING TERMINATION SIDE: GOLD FLASH over NICKEL
   SOLDER CUP ACCEPTS CABLE AWG 12-14
5. CONNECTOR IS PART MARKED: 3017W2PAM62A10X CONEC ABC

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

CUSTOMER APPROVAL DATE:

NAME: TITLE:

COMPANY NAME:

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance

dim. in mm

	date	name
drawn	01.10.10	Henneboel
appd.	01.10.10	Koch
norm		
d-old		

scale: 2:1 (5:1)

material: SEE NOTES

title:

D-SUB COMBINATION MALE

17W2P SOLDER CUP

dwg no: 13K2A3064

Inventor 10

DIN-A3

sh: 1

part no: 3017W2PAM62A10X