

Data sheet

2242.0 BS 25 GN



Mounting screw, M 2.5, Colour: Green

Business data

| | |
|--|----------------|
| Article number | 2242.0 |
| Article name | BS 25 GN |
| GTIN (EAN) | 4044211050658 |
| Packaging unit | 50 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 2.85 g |
| Weight per piece (including packaging) | 2.86 g |
| Unit of weight | G |
| Customs number | 74153300 |
| Country of origin | DE |
| Product description | Mounting screw |
| Colour | Green |

Technical data

Dimensions

| | |
|----------------|------|
| Outer diameter | 7 mm |
|----------------|------|

Connection data

| | |
|-------------------------|---------|
| Screw head | Slotted |
| Screw threading | M 2,5 |
| Tightening torque, min. | 0.4 Nm |
| Tightening torque, max. | 0.8 Nm |

Materials

| | |
|---------------------------|---------------|
| Insulation housing | Polyamide 6.6 |
| Flammability class UL 94 | V-2 |
| Working temperature, min. | -40 °C |
| Working temperature, max. | 105 °C |
| Surface screw | Nickel |

Further technical data

| | |
|----------------------|-----------|
| Mounting type | Screwable |
| Insulation available | ✓ |

Environmental Product Compliance

| | |
|--------------------------------|------------|
| REACH Conform | No |
| REACH Reference date | 2023-06-14 |
| REACH Candidate Substance Note | No |
| REACH CAS 1 Substance | LEAD |
| REACH CAS 1 Percent minimal | 0.1 % |
| REACH CAS 1 Percent maximum | 4 % |
| REACH CAS 1 Number | 7439-92-1 |
| RoHS Conform | yes |
| RoHS Exception rule | 6c |

Media

M2.5



Data sheet


2242.0 BS 25 GN



Accessories

##INVERSE##CONTA-CONNECT

Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige



| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|-----------------|---------------|----------------|
| <u>17523.2</u> | SPTK 6/LT/HB BG | 4044211209223 | 50 ST |

Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige



| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|----------------------|---------------|----------------|
| <u>17524.2</u> | SPTK 6/LT/STBI/YE BG | 4044211209919 | 50 ST |

Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige



| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>17520.2</u> | SPTK 6/DU BG | 4044211209650 | 50 ST |

Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige



| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>17521.2</u> | SPTK 6/LT BG | 4044211209162 | 50 ST |

Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige



| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>17522.2</u> | SPTK 6/QT BG | 4044211209216 | 50 ST |

Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige



| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|----------------------|---------------|----------------|
| <u>17525.2</u> | SPTK 6/LT/STBI/BU BG | 4044211209926 | 50 ST |

Data sheet

2242.0 BS 25 GN

##INVERSE##CONTA-CONNECT

Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige



| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>17521.2</u> | SPTK 6/LT BG | 4044211209162 | 50 ST |
