


Total travel position

Measuring position On horizontal

On starting position



CIRCUIT DIRGRAM

NOTE:
 Rating: DC 12V 0.1A
 Operating Force: 20±10gf
 Lifetime: 50,000 Cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
④	Contact Spring	—	1	Phosphor Bronze	Ag Clad	—
③	Terminal	—	2	Brass	Ag Plated	—
②	Base	—	1	NYLON	Black	—
①	Slider	—	1	NYLON	Cream	—

APPROVALS		DATE	TITLE:	
DRAWN	J.X.Zhang	2013/9/18	DETECTOR SWITCHS	
CHECKED			ELECTRONICS CO.,LTD	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ:	SHEET
	A		NEW				30°±0.1°	±0.30	mm	1:1	PROJ: ①	1 OF 1
							10°~30	±0.20				
							5°~10	±0.15				
							~5	±0.10				