


印字内容: E331038 9ΔAWM 2651 VW-1 105°C 300V 28 AWG NEXTRON

Code NO.	A(mm)	B(mm)	Code NO.	A(mm)	B(mm)	导体规格:28AWG 7/0.127
830-127-10C	11.43±0.15	12.70±0.15	830-127-25C	30.48±0.15	31.75±0.15	PH: 1.27±0.08mm
830-127-12C	13.97±0.15	15.24±0.15	830-127-26C	31.75±0.15	33.02±0.15	T: 0.90±0.10mm
830-127-14C	16.51±0.15	17.78±0.15	830-127-30C	36.83±0.15	38.10±0.15	印字总长: 130±20mm
830-127-15C	17.78±0.15	19.05±0.15	830-127-34C	41.91±0.20	43.18±0.20	印字空白总长: 200±20mm
830-127-16C	19.05±0.15	20.32±0.15	830-127-36C	44.45±0.20	45.72±0.20	[I2-I1]=I<0.15mm
830-127-18C	21.59±0.15	22.86±0.15	830-127-40C	49.53±0.20	50.80±0.20	[S2-S1]=S<0.15mm
830-127-20C	24.13±0.15	25.40±0.15	830-127-50C	62.23±0.20	63.50±0.20	
830-127-22C	26.67±0.15	27.94±0.15	830-127-60C	74.93±0.20	76.20±0.20	
830-127-24C	29.21±0.15	30.48±0.15	830-127-64C	80.01±0.20	81.28±0.20	

备注
1. 耐温 -25°C to 105°C
2. 绝缘体颜色 灰色



正凌精密工业(广东)有限公司
2016/11/5
内部资料请勿复印

REV.	DESCRIPTION	DATE
A	NEW RELEASED	11/2' 16

UNITS ■mm □ INCH		NAME: 1.27 FLAT CABLE ASSEMBLY	NEXTRON® NEXTRONICS ENGINEERING CORP.	
GENERAL TOLERANCES: (UNLESS SPECIFIED)		PART NO: Z-830127XXCNEX250	TITLE: CUSTOMER DWG	
	mm	INCH	APPD: 楊海文 2016/11/04	DWG NO: 010-0000-G84
4 PLACE	± **	± .**	CHKD: 廖小瓊 2016/11/04	SCALE: SHEET: REV.: 4/1 1/1 A
3 PLACE	± **	± .**	DRAWN: 陳惠枝 2016/11/4	
2 PLACE	± 0.05	± .**		
1 PLACE	± 0.1	± .**		
ANGULAR:	X'±**	.X'±2°		