



CIRCUIT DIAGRAM

Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

②	Terminal	—	5	Phosphor bronze	Au Plating	—
①	Housing	—	1	Nylon	Black	—
ITEM	PART NAME	TERN.O.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE	ELECTRONICS CO.,LTD			
DRAWN	J.X.Zhang	2013/11/11	PHONE JACKS			
CHECKED			PJ-209			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE						
			30 ^{±0.1}	±0.30	ANGLE	
			10 ^{±0.30}	±0.20	UNIT: mm	SCALE: 1:1
			5 ^{±0.10}	±0.15	±2°	DRAWING NO.
			~ 5	±0.10		SHEET 1 OF 1