


P.C.B LAYOUT(copper-sided view)



Model No.	PJ-231B-A	PJ-231B-B
Schematic		
Model No.	PJ-231B-C	
Schematic		

Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

DRAWN		J.X.Zhang		DATE		2013/11/11		TITLE:		PHONE JACKS	
CHECKED				PART NO.		PJ-231B		SCALE:		1:1	
APPROVALS				MATERIAL		Nylon		FINISHING		Black	
TERMINALS		6		REMARK				PHOSPHOR BRONZE		Au Plating	
ITEM		PART NAME		TERNO.		QTY.		UNIT:		mm	
①		Terminal		01		1		SCALE:		1:1	
		Housing		03				DRAWING NO.			
TOLERANCES ARE		30 ^{±0.1}		±0.30		ANGLE		PROJ.		SHEET 1 OF 1	
		10 ^{±0.10}		±0.20				DRAWING NO.			
		5 ^{±0.10}		±0.15		±2'		DRAWING NO.			
		~5		±0.10				DRAWING NO.			
ECN NO.		REV.		DATE.		DESCRIPTION.		CHANGE.		CHECK.	
A						NEW				APPRO.	



ELECTRONICS CO.,LTD