

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 04/27/05'	~	LJH 04/22/06'
B	ADD SCREW TYPE	DMJ 06/27/07'	~	LJC 06/27/07'
C	整理图画	YCH 05/21/08'	~	LJC 05/21/08'
F	ADD Pos TYPE	JLZ 03/29/16'	~	

NOTES:

- ELECTRICAL CHARACTERISTICS:
  - CONTACT RESISTANCE: 20mΩ Max. INITIAL.
  - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE: 1000MΩ Min.
- ENVIRONMENT CHARACTERISTICS:
  - TEMPERATURE RANGE: -40°C~+105°C.
- PART NUMBER: DS1034
- PRODUCT NUMBER CODE:  
DS1034- X X X X X X X X

- SCREW DIM. A
- Standard(W/O nut)
  - 5.00 2: 3.00 3: 5.20
  - 4.80 5: 5.80 6: 4.00
  - 4.80mm(Inside thread M2.6\*0.45p, outside thread unc#4-40)
  - 4.80mm(Inside thread M3.0\*0.5p, outside thread unc#4-40)

- SCREW TYPE
- S: Standard(W/O nut)
- CC TYPE 2: CS TYPE
  - BR TYPE 4: BRJ TYPE DIM. B: 6.00 C: 3~4mm
  - BRJ TYPE DIM. B: 6.00 C: 5~6mm
  - BRJ TYPE DIM. B: 6.00 C: 3~4mm (Inside thread M2.6\*0.45P,outside thread unc#4-40)
  - BRJ TYPE DIM. B: 6.00 C: 3~4mm (Inside thread M3.0\*0.50P,outside thread unc#4-40)














- CONTACT PLATING
- Si: FULL GOLD FLASH  
0: SELECTIVE GOLD FLASH

- SHELL PLATING
- T: FORNT & BACK SHELL TIN  
N: FORNT SHELL NICKEL,BACK SHELL TIN


- HOUSING COLOR
- B: BLACK W: WHITE  
U: BLUE

- CONNECTOR TYPE
- M: MALE F: FEMALE

- No.OF CONTACTS
- 09: 9pos. 15: 15pos. 25: 25pos.  
37: 37pos. 50: 50pos.



Dimension	Position	A±0.2	B±0.2	C±0.3	D
	9	17.90	24.99	30.80	16.33
	15	26.50	33.32	39.14	24.66
	25	40.00	47.04	53.04	38.38
	37	56.50	63.50	69.32	54.84



GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

PROJECTION	TITLE	D-SUB DIP STRAIGHT TYPE	
UNITS	mm		
SHEET SIZE	A4	SERIES	DS1034 SERIES

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1034-XXXXXXX-F		

晨翔电子有限公司  
CONNFLY CONNFLY ELECTRONIC CO. LTD