



DIMENSIONS TOLERANCE IS ±.0025 [±0.06]

THESE DRAWINGS/SPECIFICATIONS ARE THE EXCLUSIVE PROPERTY OF MICRO-MEASUREMENTS. THEY SHALL NOT BE REPRODUCED OR COMMUNICATED TO OTHERS, IN WHOLE OR IN PART, NOR BE USED AS A BASIS FOR MANUFACTURE OR SALE OF THE ITEMS REPRESENTED, WITHOUT THE WRITTEN PERMISSION OF MICRO-MEASUREMENTS.



Micro-Measurements
Raleigh, North Carolina USA



125SL PATTERN LAYOUT

CONSTRUCTION:

C4A

OPTIONS:

RESISTANCE:

350±0.3%
120±0.3%

REFERENCE:

DRAWN BY:

OS

PROJ. ENG.

AH

DATE:

2018-02-28

DATE:

2018-02-28

SCALE:

N.T.S.

DWG. #

MS-125SL-10520

ALL DIMENSIONS ARE IN INCHES [mm].

REVISION:

~

1. MicroMeasurements Advanced Sensors C4A Strain Gages are packaged in a rugged carton box for product protection and ease of usage



Engineering data is on the backside label

2. Standard package includes 10 gages per box, each gage is packaged in an individual Acetate bag



3. Gage is protected with an Acetate folder, wires are wound into a coil and bound with a tie twist for easy wire handling



For technical questions, contact mm@vpgsensors.com