


目录 MAPY	设置内容 MODIFICATION	日期 DATE
------------	----------------------	------------



特性: Specifications:

电气: Electrical:

1. 接触阻抗: Contact Resistance: 30 milliohms MAX
2. 耐电压: Dielectric With Standing Voltage: 500 V AC AT Sea Level
3. 绝缘阻抗: Insulation Resistance: 1000 MEGA ohms MIN

机构: Mechanical:

1. 结合力: Mating Force: 40 N MAX 最大 40 N
2. 拔出力: Unmating Force: 7 N MIN 最少 7 N

材料: Material:

1. 塑胶: PBT.
 2. 端子: Contact: C2680
 3. 外壳: Shell: SPCC
- 电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area: Tin/Lead On Solder Talls. 接触点镀金, 脚镀锡
2. 外壳: Shell: Nickel Plating . 镀镍

PCB LAYOUT

公差表		公差表	
TOLERANCE UNLESS OTHERWISE		UNLESS OTHERWISE	
X	±0.30	X'	±G'
X	±0.25	X''	±J
XX	±0.20	XX'	±J'

未标注的公差按一般标准计算

单位 UNITS	MM	制图 DRAWING	客户料号 PURCHASER PART NO.
比例 SCALE	1:1	审核 CHKD	产品名称 PRODUCT NAME
日期 DATE	2014/04/23	核准 APPD	角法 ANGLE
			版本 VER
			A0

