

Section: A-A

电气性能/Electrical

参考标准/Standard: UL IEC  
 额定电压/Rated voltage: 300V 320V  
 额定电流/Rated current: 15A 20A  
 接触电阻/Contact resistance: 20mΩ  
 耐电压/Withstanding voltage: AC2000V/1Min  
 绝缘电阻/Insulation resistance: 500MΩ/DC500V

机械性能/Mechanical

温度范围/Temp.Range: -40° C~+105° C  
 瞬间温度/MAX Soldering: +250° C, for 5 Sec


尺寸/Dimensions

间距/Pitch: 5.00mm, 5.08mm  
 极数/Poles: 2P-24P

材质及电镀/Material

塑件/Housing: PA66, UL94V-0  
 焊针/Pin header: Brass, Tin plated  
 螺母/Nut: M2.5 Brass

订购方式:  
HOW TO ORDER



TOLERANCES EXCEPT AS NOTED

variable range	linear dimension				fillet	chamfer	short angle sid			≡	—	□	//	⊥			
	to	over	over	over	to	to	to	to	to								
to 6	6 to 30	30 to 120	120 to 480	to 480	all	to 6	to 10	to 10	to 50	to 120	to 10	to 120	to 120				
tolerance	±0.1	±0.2	±0.3	±0.5	±0.9	±0.2	±0.5	±1	1°	30'	20'	10'	0.5	0.025	0.06	0.12	0.4

单位/UNITS	mm	尺寸/SIZE	A4	比例/SCALE	第一视角/FIRST ANGLE PROJECTION	
Cixi Dibo Electronics Co.,LTD					名称/NAME	DB2ERM-5.08-XXP-F