

SPECIFICATIONS

Rated(额定参数): 150V,10A
 Dielectric strength(抗电强度): AC1500V/1 Minute
 Insulation Resistance(绝缘电阻):1000MΩ Min
 Contact Resistance(接触电阻):20mΩ Max
 Screw Torque(扭矩): 0.2Nm (1.7Lb.in)
 Wire Range(线径):26~16AWG
 Strip length(剥线长度):5~6mm
 Temp. range(操作温度): -40°C~+105°C
 MAX Soldering(瞬时温度):+250°C,5s

Housing Material(塑件): PA66 (UL94 V-0)
 Contact(端子): Brass, Tin plating(黄铜镀锡)
 Wire protector(弹片): Brass(黄铜), Ni plating(镀镍)
 Screw (螺丝): M2.0, Steel, Zinc plating(钢,镀锌)

PITCH RANGE		NOMINAL DIMENSION RANGE	
IN	MM	IN	MM
OVER	6	OVER	30
TO	10	TO	60
OVER	10	TO	100
TO	24	TO	150
±0.10	±0.15	±0.25	±0.30
		±0.30	±0.50
		±0.50	±0.70
		±1.00	±1.00

Ordering Information




JL 124D - XXX XX X X 1

Pitch
 350=3.50PH
 381=3.81PH
 396=3.96PH

No.of pins
 2P,3P,4P~24P

Housing Color
 B=Black
 G=Green
 U=Blue
 R=Red
 W=White
 Y=Yellow
 O=Orange
 E=Grey

Packing
 O=Pe bag
 T=Tube
 A=Troy



Recommended P.C.B Layout(Top Side)

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	BEN	17.01.03	SCALE	FIT	SHEET	PROU.	PART NO.	TITLE:
				XX	±									
A0	2017.01.03	NEW DRAWING		X:XX	±	CHECK			mm	A4	1/1		JL 124D-XXXXXXXX1	3.50/3.81/3.96mm Terminal Blocks
1			4	Angle	±3'	APPROVE								Femle 180°

JIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992