







① 06011WP HY36M-B




ISO VIEW







SECTION A-A(1/1)



② F/H 06011WP HY36M-OR



ISO VIEW



- NOTE -

- BEFORE USING, CHECK THE HARMFUL CRACK, BURR, ETC.
- GENERAL TOLERANCES - SEE BELOW.
- MARKING & CAV No. BY AS GENERAL RULE OF KUM
- ASSY PART

- FRONT HODLER : HP651-36100
- CONNECTOR CLIP : GC110-03020
- TERMINAL

Application Wire(Sq)	PART NAME	PART No
0.3 ~ 0.5 SQ	TML NWP-M-S	TP161-00100
0.75 ~ 1.25 SQ	TML NWP-M-M	TP161-00200
2.0 ~ 3.0 SQ	TML NWP-M-L	TP161-00300
0.3 ~ 0.5 SQ	TML NWP-M-S-Au	TP161-00110
0.75 ~ 1.25 SQ	TML NWP-M-M-Au	TP161-00210
2.0 ~ 3.0 SQ	TML NWP-M-L-Au	TP161-00310
0.22 SQ	TML AWP-M-SS	TP131-00400
0.3 ~ 0.5 SQ	TML AWP-M-S	TP131-00100
0.75 ~ 1.25 SQ	TML AWP-M-M	TP131-00200
0.22 SQ	TML AWP-M-SS-Au	TP131-00410
0.3 ~ 0.5 SQ	TML AWP-M-S-Au	TP131-00110
0.75 ~ 1.25 SQ	TML AWP-M-M-Au	TP131-00210

4) Wire Seal

Insulation Nominal Diameter	PART NAME	PART No
Φ1.4~Φ1.8	W/S NWP-3.6S(R)	EM010-00060
Φ1.9~Φ2.2	W/S NWP-2.8S(MB)	EM010-00140
Φ2.3~Φ2.7	W/S NWP-2.3S(GY)	EM010-00120
Φ2.8~Φ3.3	W/S NWP-1.9S(GN)	EM010-00030
Φ3.6~Φ4.0	W/S NWP-1.4S(OR)	EM010-00100
CLOSED SEAL	W/S NWP-V(BR)	EM010-00050
Φ0.9~Φ1.3	W/S AWP 0.9S(MB)	EB010-01140
Φ1.4~Φ1.8	W/S AWP 1.4S(BR)	EB010-01050
Φ1.9~Φ2.2	W/S AWP 1.9S(GN)	EB010-01030
Φ2.3~Φ2.6	W/S AWP 2.3S(GY)	EB010-01120
Φ2.7~Φ2.9	W/S AWP 2.7S(OR)	EB010-01100
CLOSED SEAL	W/S AWP-V(R)	EB010-01060

5. THIS PART IS WATERPROOF CONNECTOR.

APV	DATE	NOTE No.	SYM	ALTERATION	DWN
CJW	16.07.29	E016-0313	△	ADDED SHAPES(4EA)	LJW
CJW	14.08.27	E012-0211	△	RELEASED	LDW

NO.	PART NAME	PART No.	COLOR	MATERIAL
②	F/H 06011WP HY36M-OR	HP651-36100	ORANGE	PBT
①	06011WP HY36M-B	HP641-36020	BLACK	PBT

DRAWING NAME	06011WP HY36M-B
DRAWING No.	HP641-36020-C01A

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	150MAX	200MAX	200VR	ANGLE
A	±0.2	±0.3	±0.5	±0.8	±1.0	±1.4	±30'

THIRD ANGLE PROJECTION	A	1/2(1/1)	LDW	LDW	KNJ	CJW
TOLERANCE		SCALE	DESIGN	DRAWN	CHECKED	APPROVED

**KUM** 케이유엠