



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:10,000cycles



CIRCUIT DIAGRAM



Φ 3.5, MATE PLUG

②	Terminal	5	Phosphor bronze	Au Plating		
①	Housing	1	Nylon	Black		
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE			
DRAWN				TITLE: PHONE JACKS		
CHECKED				PART NO. PJ-S32545		
APPROVALS						
TOLERANCES ARE		30~0.3	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			PROJ:
		5~10	±0.15			
		~ 5	±0.10	±2'	DRAWING NO.	SHEET 1 of 1

ECN NO.	REV.	DATE.	NEW	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A						