


Kinghelm®

KHB(RG113)-55-29

REV. NUMBER		DESCRIPTION		DWN	CHK	DATE
A		DESIGN				



NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING:DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE:3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPENS/SHORT, MISWIRING AND INTERMITTENT FAILURES
2. MATERIAL:
 - 2.1. SEE TABLE
3. MECHANICAL:
 - 3.1. SMA PULL FORCE: 12.0KGS.
4. ALL COMPONENTS ARE ROHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿I-PEX, 1.13端子, 镀金	1
②	接头	SMA母头内孔, 分体, 11牙, 镀金	1
①	同轴线	RF 1.13 黑色线,OD:1.13mm	AS

金航标电子有限公司

ALL DIMENSION ARE IN MM		DRAWN	DATE	TITLE	
COMPUTER GENERATED IN SOLIDWORKS		Janny	2018/05/04	RF CABLE	
DO NOT SCALE THIS DRAWING		ENG.		I-PEX 1.13 TO SMA / F L=55 MM	
PROJECTION		MFG.		SIZE	REV
GENERAL TOLERANCE FOR ANGLES ± 1° ± 0.3 ± 0.25 ± 0.150		Q.A.		B	A

CUSTOMER P/N:

4

3

2

1

A

B

C

D

A

B

C

D