





NOTES:
 Voltage Rating:250V AC/DC
 Current Rating:3.0A AC/DC
 Dielectric Withstand Voltage:500V AC/minute
 Contact Voltage:20M Max.
 Insulation Voltage:1000M Min
 Operation temperature:-40 °C to +105 °C
 Insulator Material:Polyester.Ul94V-0
 Contact Material:Brass
 Contact Plating:AuorSn Plated on Nickel Overall

Recommended P.C.B Layout
 P.C.B Board Tolerance±0.05



Dimension antitheses list		
item	PC	L
Standard	3.00	16.0/21.0
Alternate	---	---

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司		SHEET	1/1
				X.	±0.30	X°	±5°	CONNECTORS XFCN CONNECTORS CO., LTD.		DATE	2010. 4. 12
				.X	±0.20	.X°	±2°	PRODUCT NAME	2.54mm Box Header Connectors	UNITS	mm
				.XX	±0.08	.XX°	±1°	PART. NO.	BH254R-XX	SCALE	1:1
AO	MODIFICATION		DRAW	DATE	.XXX	±0.03	.XXX°	VIEW	⊕	DWG NO.	009