





Recommended P.C.B Layout  
P.C.B Board Tolerance±0.05

NOTES:

Voltage Rating:250V AC/DC  
Current Rating:3.0A AC/DC  
Dielectric Withstand Voltage:500V AC/minute  
Contact Voltage:20M Max.  
Insulation Voltage:1000M Min  
Operation temperature:-40 °C to +105 °C  
Insulator Material:Polyester.UL94V-0  
Contact Material:Brass  
Contact Plating:AuorSn Plated on Nickel Overall



塑胶高度可选 (mm)				常用
H	1.0	1.5	2.0	2.54

Dimension antitheses list				
item	PA	---	PC	L
Standard	6.00	---	3.00	11.50
Alternate	---	---	---	---

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	<b>XFCN兴飞连接器有限公司</b> CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	$\pm 0.30$	X°	$\pm 5^\circ$			CHKD	DATE
				.X	$\pm 0.20$	.X°	$\pm 2^\circ$	APPD	PRODUCT NAME	2.54mm Pin Header Connectors	
				.XX	$\pm 0.08$	.XX°	$\pm 1^\circ$	VIEW	PART. NO.	SCALE	1:1
AO	MODIFICATION		DRAW	DATE	.XXX	$\pm 0.03$	.XXX°			$\pm 0.5^\circ$	DWG NO.