



EVA washer x1pcs  
(FSU-PA01)



**SPECIFICATIONS**

- Max. current/voltage rating with resistive load:** 400mA 32VAC - 100 mA 50VDC - 125 mA 125VAC.
- INITIAL CONTACT RESISTANCE:** 50 mΩ max.
- INSULATION RESISTANCE:** 1 GΩ min. at 500VDC.
- DIELECTRIC STRENGTH:** 1,000 VAC rms.
- ELECTRICAL LIFE AT FULL LOAD:** 500,000 cycles.
- PANEL THICKNESS:** 0.8 mm (.031) min. -1.8 mm (.071) max.
- TOTAL TRAVEL:** 1.5 mm (.059).
- OPERATING FORCE:** 2N~5N.
- CONTACT BOUNCE:** 10 ms.
- MECHANICAL LIFE:** 1,000,000 cycles.
- SOLDERING:** 350°C max. for 5 seconds.

**MATERIALS**

- CASE:** Diallyl phthalate (DAP)(UL94v-0).
- CAP:** Polyamide 6/6.
- BUSHING:** Polyamide 6/6.
- TERMINAL/CONTACTS:** Gold over silver plated.
- RoHS & Lead Free**

Model No.	POS.1	POS.2
PAS6	OFF	MOM
Term. Comm.	OPEN	SHORT
SCHEMATIC		

SWITCH FUNCTION

德利威電子股份有限公司  
DAILYWELL ELECTRONICS CO.,LTD.

符號	原尺寸	修改後尺寸	變更日期	SCALE (比例) : 3 : 2 TOLERANCE (公差) : 0.00 mm ± 0.25mm 0.0 mm ± 0.40mm ANGULAR : ± 5° FILE NAME : PASP0414	TITLE 圖名	Sub - Miniature Pushbutton Switches		SIZE 圖紙	A4	
1	Ⓐ	依據N1607修訂FSU-PA01尺寸公差	MAY-27-2016		DWG NO. 圖號	PAS6B1M1CES3-5		UNIT 單位	inch mm	
2	Ⓑ				REV. 版本	B	DATE 日期	DEC - 10 - 2014	SHEET 張數	1 of 1
3	Ⓒ				CHECKED BY 審核			DRAWN BY 製圖	IRENE	
4	Ⓓ									
5	Ⓔ									