





XKB

Specificationsxxb


规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥500MΩ
 绝缘电阻: ≥500MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ XKB
 After environmental testing:≤30mΩ
 环境测试后: ≤30兆欧



X8821 W V X-XX L -N0 SN

- ◎Series No.
- ◎Category:W-WAFER
- ◎Welding Board Angle: V-180°
- ◎Welding Way:S-SMT
- ◎Row No. Pin No.: XX-Single Row;
- ◎Plug the Pin&Special No.:L-With Lock
- ◎Material:NO-PA66 94V-0
- ◎Plating Category: SN-Bright Tin Plating

Poles	Dimension mm		Poles	Dimension mm	
	A	B		A	B
2	2.50	7.50	10	22.50	27.50
3	5.00	10.00	11	25.00	30.00
4	7.50	12.50	12	27.50	32.50
5	10.00	15.00	13	30.00	35.50
6	12.50	17.50	14	32.50	37.50
7	15.00	20.00	15	35.00	40.00
8	17.50	22.50	16	37.50	42.50
9	20.00	25.00			



广东星坤科技股份有限公司
 Relays, Switches, Connectors
 General Tolerance±0.05

生 日期
 發 日期
 Δ% 文件工程章
 REVISIONS
 www.heloxkb.com

X8821WV-XXL-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X8821H-L
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWVN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	2.54 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

XKB	ANGLAR	±5°
	L ≤ 4	±0.2
	4 < L ≤ 16	±0.3
	16 < L ≤ 63	±0.4
	L > 63	±0.5
UNSPECIFIED TOLERANCES		