



F: Flat

S: Scrolls

ΔX	ΔX	ΔX	MARK
DESCRIPTION	REVISIONS	DATE	REVISED
DATE	APPROVED	UNSPECIFIED TOLERANCES	
ANGULAR	±5°		
$L \leq 4$	±0.2		
$4 < L \leq 16$	±0.3		
$16 < L \leq 63$	±0.4		
$L > 63$	±0.5		

DSND	DATE	MODEL TYPE:	DP CONNECTOR
DWN	DATE	SCALE:	N/A
CHKD	DATE	VIEW:	3/4
APPD	DATE	UNIT:	mm
APPD	DATE	SIZE:	A4
XKB INDUSTRIAL PRECISION CO., LIMITED		DWG NO.:	CAR02-201ENXX
WEIGHT	1.0g	SHEET	1/1
		REVISION	A0

- NOTES:
1. MATERIAL: HOUSING: THERMOPLASTIC HIGH TEMP WITH 30% GF. PART HOUSING: COP ESTYL 6711 OR 6871 (P/US)S40.
 - CONTACT: CARBON/RT-TRADIMIN
 - SHELL: CARBON/RT-TRADIMIN
 - WULFR: KAPTON TAPE 100UMIN
 2. PLATING: CONTACT: 10% MIN GOLD PLATING ON CONTACT AREA. GOLD FLASH PLATING OVER ALL SHEET: 50-80% NICKEL PLATING OVER ALL.
 3. SOLENTIAL COMPLAINTY (U) (M) (K)
 4. PART NO. DESCRIPTION:
- QWQZ-20-1 E N X X
 (1) DISPLAY PORT (2) SHELL PLATING
 (3) POS NO. (4) NICKEL PLATING
 (5) PACKAGE (6) STAFFE REEL (M) (V) (W)
 (7) HOUSING COLOR (8) STAFFE REEL (M) (V) (W)
 (9) FINISH (10) INTERFACE TYPE
 (11) CONTACT PLATING (12) SERIALS
 (13) E-CLASS (14) MATERIAL