



view A
scale 1:1


| FREE | | | LOCK | | |
|------|---|---|------|---|---|
| 1 | 2 | 3 | 1 | 2 | 3 |
| ○ | ○ | ○ | ○ | ○ | ○ |
| 4 | 5 | 6 | 4 | 5 | 6 |
| ○ | ○ | ○ | ○ | ○ | ○ |



| | |
|------|-----|
| FREE | 9.1 |
| LOCK | 7.2 |



View A



| SPECIFICATION | |
|-------------------------------|---------------|
| 1.环境温度(Operating Temp) | -20℃~+80℃ |
| 2.相对湿度(Working Humidity) | 5%~35% |
| 3.额定规格(Rated Value) | DC50V/30mA |
| 4.接触电阻(Contact Resistance) | 100mΩ max |
| 5.绝缘电阻(Insulation Resistance) | 100MΩ min |
| 6.耐电压(Withstand Voltage) | 250Vac/60S |
| 7.动作力(Operating Force) | 250±50gf |
| 8.使用寿命(Operating Life) | 100,000 cycle |

| 序号 NO. | 零件名称 PART NAME | 数量 Q'TY | 材质 MATERIAL |
|--------|----------------|---------|----------------------|
| 7 | Crochet Hook | 1PCS | Carbon Steel |
| 6 | Spring | 1PCS | Carbon Steel |
| 5 | Contact Chip | 2PCS | Silver-Coated Copper |
| 4 | Terminals | 6PCS | Copper plated Silver |
| 3 | Panel | 1PCS | LCP Natural Color |
| 2 | Keypad | 1PCS | LCP Black |
| 1 | Housing | 1PCS | LCP Black |

| | | | | | |
|---|---------------|------------|-------------|------|--------------------------------------|
| 东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd. | | | | | |
| 普通公差 common tolerance: 0~5±0.15; 5~10±0.3; 10~30±0.5; 角度angular: ±0.5°; | 制图 DRAWN | JEFF | | | 品名Title: 7x7平头无锁开关 Push Switch |
| | 日期 DATE | 2018-7-18 | 单位 UNIT | mm | |
| | 审核 CHECKED | JEFF | 比例 SCALE | free | 料号Part NO. |
| 核准 APPROVED | JEFF | 尺寸 SIZE | A4 | | |