

环保物料

TEL:0769-82001899

- 1 座架材料 (Seat materials): Black Thermoplastic ULLK'ó Ö94 V0
- 2 端子原材料 (Terminal raw materials) H62KpKXH62 nickel plating
- 3 焊接性 (Solderability) max. 260 °C, 10 s (Wave)
- 4 适合电路板装配 (Suitable for circuit board assembly)
- 5 装配方式 (Assembly way) • 插 (insert, welding)
- 6 认证 (Agency Approvals)

For Fuse	Rated Amp	Rated Voltage	Operating Power	Contact Resistance	Insulation Resistance	Dielectric Strength
F 1.0	10 A	250 V	1.6 W	≤ 10 mΩ	≥ 1000 MΩ	3000 V
5x20mm	10A	250V	1.6W	! 0	! 0	>300Vac/60"

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	<b>XFCN 兴飞连接器有限公司</b> CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30	X°	±5°			CHKD	DATE
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	5X20mm '• ‡	
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	PTF-15	
AO	MODIFICATION			DRAW	DATE	.XXX	±0.03	.XXX°	±0.5°	DWG. NO.	009