



Mounting holes

- 1 材料 (Seat materials): Black Thermoplastic (UL94 V0)
- 2 端子材料 (Terminal raw materials) H62Kp (H62 nickel plating)
- 3 焊接性 (Solderability) max. 260 °C, 10 s (Wave)
- 4 适用性 (Suitable for circuit board assembly)
- 5 装配方式 (Assembly way) • 插 (insert, welding)
- 6 认证 (Agency Approvals)

For Fuse	Rated Amp	Rated Voltage	Operating Power	Contact Resistance	Insulation Resistance	Dielectric Strength
F 1	10A	250V	1.6W	≤ 10mΩ	≥ 1000V	6@9
5x20mm	10A	250V	1.6W	! 0	! 0	>300Vac/60"

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN 兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1	
				X.	±0.30	X°	±5°			CHKD	DATE	2010. 4. 12
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	5X20mm 1 2	UNITS	mm
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	PTF-77	SCALE	1:1
				.XXX	±0.03	.XXX°	±0.5°				DWG. NO.	009
AO	MODIFICATION	DRAW	DATE									