

10  
1 2 3 4 5 6 7 8 9  
A  
环保物料

TEL:0769-82001899

ATO Blade Fuse Holder  
Electrical :MAX 30A 60V dc  
Material Brass Nickel plated  
Insulator material PA66  
Insulation Resistance: At 500V DC:100M $\Omega$  Min  
Contact Resistance Max.50M $\Omega$   
Dimensionless Unit mm  
Dimension Tolerance of 0.25

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	<b>XFCN</b> 兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.	SHEET	1/1
				X.	$\pm 0.30$	X°	$\pm 5^\circ$		CHKD	DATE
				.X	$\pm 0.20$	.X°	$\pm 2^\circ$	APPD	PRODUCT NAME	ATO ZVñ'•‡
AO				.XX	$\pm 0.08$	.XX°	$\pm 1^\circ$		PART. NO.	XF-101
VER	MODIFICATION	DRAW	DATE	.XXX	$\pm 0.03$	.XXX°	$\pm 0.5^\circ$	VIEW	DWG. NO.	009