





LAYOUT PROHIBITION AREA

S: Scrolls



F: Flat

Housing Material: PA9T UL94V-0, Black
 Contact Terminal: COPPER ALLOY. (T=0.25mm)
 Metallic Shell: Brass (T=0.30mm)

U221-04XN-3BU06-X5
 1: Au 1U'
 5: Au 15U'
 6: Au 30U'
 5: BRASS
 S: Scrolls F: Flat
 W/WHITE B:BLACK
 1: PBT
 2: PA6T
 3: PA9T
 4: LCP

MARK	DESCRIPTION	REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX						
ΔX						
ΔX						
ΔX						

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	USB 2.0
CHKD	DATE	UNIT: mm	PART NO.: U221-04XN-3BU06-X5
APPD	DATE	SIZE: A4	DWG NO.: U221-04XN-3BU06-X5
XKB INDUSTRIAL PRECISION CO., LIMITED			
WEIGHT	SHEET	REVISION	
1.09	1/1	A0	