



HSF

NOTES:
 Rated Current: 3.0AMP
 Contact Resistance: 20mΩ max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ min
 Operation Temperature: -25℃ to +85℃

 Insulator Material: PA66+30%G.F UL94V-0
 Use with: WF2543-T
 Mated with: WF2543-Wafer




Specification & Ordering Information:

Circuit	Part No.	Dimension	
		A	 B
2x01	WF2543-2H01X01	2.54	5.1
2x02	WF2543-2H02X01	2.54	5.08
2x03	WF2543-2H03X01	5.08	7.62
2x04	WF2543-2H04X01	7.62	10.16
2x05	WF2543-2H05X01	10.16	12.70
2x06	WF2543-2H06X01	12.70	15.24
2x07	WF2543-2H07X01	15.24	17.78
2x08	WF2543-2H08X01	17.78	20.32
2x09	WF2543-2H09X01	20.32	22.86
2x10	WF2543-2H10X01	22.86	25.40
2x11	WF2543-2H11X01	25.40	27.94
2x12	WF2543-2H12X01	27.94	30.48
2x13	WF2543-2H13X01	30.48	33.02
2x14	WF2543-2H14X01	33.02	35.56
2x15	WF2543-2H15X01	35.56	38.10
2x16	WF2543-2H16X01	38.10	40.64
2x17	WF2543-2H17X01	40.64	43.18
2x18	WF2543-2H18X01	43.18	45.72
2x19	WF2543-2H19X01	45.72	48.26
2x20	WF2543-2H20X01	48.26	50.80

Ordering Information

WF2543 - 2 H XX X 0 1

No. of Row: Dual Row
 No. of pins: 01P-20P
 Color: W=White, B=Black
 Packing: 0=PE Bag



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW SU	DATE	SCALE	FIT	PART NO.
A2	2019/11/08	MODIFY MATERIAL	---	X.X ±0.40	SU	2019/11/08	UNIT	mm	SEE TAB
A1	2012/11/19	MODIFY DIM "B"	---	X.XX ±0.25	CHECK	DATE	SIZE	A4	TITLE:
AO	2012/09/08	NEW	---	X.XXX ±0.15	APPROVE	DATE	SHEET	1/1	DUAL ROW 2.54 HOUSING
				Angle ± 3'			PROJ.		Customer NO.

WCON

Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com
 WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com