



Model NO	PJ-619
Schematic	

Rating: 0.5A 30V DC
 Contact Resistance: 100 mΩ Max.
 Operating temperature: -25℃ ~ 80℃
 Operating force: 3-20N
 Operating Life: 5,000 cycles

②	Shunt terminal	---	6	Phosphor bronze	Plating Au	---
①	Housing	---	1	PPA	Black	---
ITEM	PART NAME	Serial number	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE	TITLE: PHONE JACKES			
DRAWN		QIFENG.XU	2019/8/8	ELECTRONICS CO.,LTD		

CHECKED		PART NO.		SCALE: 1:1		PROJ:	
APPROVALS		TITLE: PHONE JACKES		SCALE: 1:1		PROJ:	
TOLERANCES ARE		30~0.15	±0.30	ANGLE	UNIT: mm	SHEET 1 OF 1	
CHANGE.		10~0.30	±0.20	±2°	DRAWING NO.	SHEET 1 OF 1	
CHECK.		5~0.10	±0.15	±2°	DRAWING NO.	SHEET 1 OF 1	
APPRO.		~ 5	±0.10	±2°	DRAWING NO.	SHEET 1 OF 1	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	
	A		NEW				