


P C B Layout(Top view)



Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:—20℃~70℃  
 Operating force:3—20N  
 Operating Life:5,000cycles

Model NO	PJ-316C-A	PJ-316C-B	PJ-316C-C
Schematic			
Model NO	PJ-316C-D	PJ-316C-E	PJ-316C-F
Schematic			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
DRAWN xu qi feng 2014/9/19						
CHECKED						
APPROVALS						
TOLERANCES ARE						
30~12.5	±0.30	ANGLE	PART NO.	SCALE: 1:1	PROJ:	SHEET 1 OF 1
10~30	±0.20	UNIT: mm	TITLE: PHONE JACKS			
5~10	±0.15	DRAWING NO.				
~5	±0.10					
ELECTRONICS CO.,LTD						
HPPD						
MATERIAL PHOSPHOR BRONZE PLATING AU						
FINISHING BLACK						
REMARK						