



Material:

* Insulation:

Glass filled Polyamide UL 94V-0
Color Black

* Contact: Copper alloy, t=0.2mm

* Fixed Tab: Brass, t=0.2mm

* Plating code: Gold flash over Nickel

DIM.A = 0.50 * No. of Spaces

DIM.B = DIM.A + 3.0

DIM.C = DIM.A + 0.5

* Available in 10 through 80 circuits

X1015 W M-XX X-X

① ② ③ ④ ⑤ ⑥

① Series No.

② Category: W-WAFER

③ Welding Board Angle: M-Male

④ No. of Circuits

⑤ Special No: S-With Positioning Column

⑥ Height:

A: Dim.D = 2.0mm (Circuits: 10~80pin)

C: DIM.D = 3.0mm (Circuits: 10~60pin)

D: DIM.D = 3.5mm (Circuits: 10~60pin)

					ANGLAR	±5°	DSND		DATE		SCALE: N/A	MODEL TYPE:		
					L ≤ 4	±0.2	DWN		DATE		VIEW:	BTB CONNECTOR		
					4 < L ≤ 16	±0.3	CHKD		DATE		UNIT: mm	PART NO.:		
					16 < L ≤ 63	±0.4	APPD		DATE		SIZE: A4	DWG NO.:		
					L > 63	±0.5						X1015WM-XXX-X		
REVISIONS					UNSPECIFIED TOLERANCES		KKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												1.0g	1/1	A0