




MARK 記号	REVISION 来歴	DATE 年月日	SIGN 担当	APP. 承認



P. C. BOARD LAYOUT (S=10:1)
Tolerance: ±0.03

- NOTE
- 1. SPEC: CPB9406B0118E
 - 2. PACKAGE: CPB9406N0118E
 - 3. COPLANARITY: 0.08MAX



15 DIMENSIONS RANGE	TOLERANCE UNLESS SPECIFIED
0.5 ≤ X < 1	±0.15
1 ≤ X < 6	±0.20
6 < X < 18	±0.30
18 < X < 50	±0.50
50 < X < 120	±0.70
120 < X < 250	±0.90
250 < X < 500	±1.20

ITEM 部番	PART NO. 番	NAME 名称	MATERIAL 材質	FINISH 処	Q'TY 員数	NOTE 備考
3	501CPB-036-ZZF	HOLD DOWN	Cu ALLOY t=0.08	SnALLOY	2	
2	415CPB-124-ZZF	CONTACT	Cu ALLOY t=0.08	AuPLATE	6	
1	101CPB-196-06F	HOUSING	LCP (GF)	BLACK	1	

UNIT 単位	mm	SCALE 尺度	20:1	DESCRIPTION 名称	P=1.3mm H=0.9mm F-B CN	ISSUED 出
APPROVED 承認	CHECKED 検	TRACED 写	DESIGNED 設計	463B	SOCKET	
Mar-6'18 <i>F. Ishida</i>			Mar6'18 Y. Ishida	DRAWING NO. 番 CPB9406-0118E		

CONFIDENTIAL