



PANEL CUT-OUT			
Z	Y	X	
0.70~1.25	14.50~14.70	14.40~14.60	14.60~14.70
1.25~2.00	14.50~14.70	14.60~14.70	14.60~14.70

NOTES:

1. Rating:
VDE ENEC 3A 250VAC T125/55
UL cUL 6GPA 125VAC/3GPA 250VAC T105/55
COC 3A 250VAC, 3A/40A 250VAC T105/55
2. Circuit Diagram: 2P ON-OFF
3. Terminal Strength: $\geq 80N$
4. Electrical life: ≥ 10000 cycles
5. Withstand Voltage: $\geq 1500VAC$ 1min
Terminals to Button: $3000VAC$ 1min
Leakage Current: 1mA
6. Current resistance: $\leq 50m\Omega$ (initial)
7. Insulation resistance: $\geq 100M\Omega$
8. Body Material: NYLON 66 94V-0-2

普通公差:
COMMON TOLERANCE:

UP TO 5	± 0.20
ABOVE 5 TO 30	± 0.30
ABOVE 30	± 0.50
ANGULAR	$\pm 5^\circ$

LECI 乐磁电子有限公司
LECI ELECTRONICS CO., LTD

单位 UNIT	mm	投影 PROJECTED	Φ	品名 PRODUCT NAME	跷板开关	比例 SCALE	Free
绘图 DRAWN BY	周金勇	核对 CHECKED BY	梁金勇	型号 MODEL NO.	RS601H		
日期 DATE	2015.11.21	核准 APPROVAL BY	周培雷	图号 DWG NO.	RS601H2-1010016BB		

A4			
A3			
A2			
A1			
REV.	DATE	REVISION DESCRIPTION	ISSUE