



PANEL CUT-OUT		
Z	Y	X
0.70~1.25	10.50~10.70	28.9~29.1
1.25~2.00	10.50~10.70	29.1~29.2
2.00~3.00	10.50~10.70	29.2~29.3



NOTES:

1. Rating:

VDE ENEC 16(4)A 250V AC T85

KC 16(4)A 250V AC T85

CQC 16(4)A 250V AC T105/55

UL cUL 16GPA 125V AC/16GPA 250V AC T105/55

2. Circuit Diagram: 2P ON-OFF

3. Terminal Strength: ≥80N

4. Electrical life: ≥10000 cycles

5. Withstand Voltage: Withstand Voltage: 1500VAC 1min
Terminals to Button: 3000VAC 1min
Leakage Current: 1mA

6. Current resistance: ≤50mΩ (initial)

7. Insulation resistance: ≥100MΩ

8. Body Material: NYLON 66 94V-0-2

A4				普通公差:		<h1 style="text-align: center;">LECI</h1> <h2 style="text-align: center;">乐磁电子有限公司</h2> <p style="text-align: center;">LECI ELECTRONICS CO., LTD</p>							
A3				COMMON TOLERANCE :									
A2				UP TO 5	±0.20	单位	mm	投影	⊕	品名	跷板开关	比例	Free
A1				ABOVE 5 TO 30	±0.30	绘图	周金勇	核对	梁金勇	型号	RS606		
REV.	DATE	REVISION DESCRIPTION	ISSUE	ABOVE 30	±0.50	日期	2015.8.17	核准	周培雷	图号	RS606-1010011CBB		
				ANGULAR	±5°	DATE		APPROVAL BY		DWG NO.			