




1 : 1



1) maximales Anzugsmoment: 200 Ncm  
max. torque: 200 Ncm

144132	6 - 8	12	
144131	2.5 - 6	9.7	
Ident.-Nr.	Leiterplattenstärke T / thickness of pcb	A	
Information:		Tolerances ISO 2768-m	Scale 2:1
		 All Dimensions in mm	
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.	Designation <b>Führungsbolzen, Bausatz ERmet Guiding System, Kit</b>
		 www.ERNI.com	<b>144130</b>
g	20.01.2005		1
Index	Date	V:00045528.SZA	ERMBGR

Consider protection memo from DIN 94