



PowerSync®  
包尔星克



## 180度二插对180度公对母延长线

- 线材通过3C认证
- 抗摇摆设计，线身耐弯曲
- 纯铜线芯，阻燃线材，耐高温
- 高韧性外被材质,韧度有效提升,不易受外力拉扯断
- 原产地:中国上海

型号	长度/m	线材规格	外被线径/mm
MPCNKF0005	0.5	RVV 2C*1.5mm <sup>2</sup>	7.8±0.2
MPCNKF0010	1.0	RVV 2C*1.5mm <sup>2</sup>	7.8±0.2
MPCNKF0015	1.5	RVV 2C*1.5mm <sup>2</sup>	7.8±0.2
MPCNKF0020	2.0	RVV 2C*1.5mm <sup>2</sup>	7.8±0.2
MPCNKF0030	3.0	RVV 2C*1.5mm <sup>2</sup>	7.8±0.2
MPCNKF0050	5.0	RVV 2C*1.5mm <sup>2</sup>	7.8±0.2
MPCNKF0100	10	RVV 2C*1.5mm <sup>2</sup>	7.8±0.2
MPCNKF0150	15	RVV 2C*1.5mm <sup>2</sup>	7.8±0.2