



PowerSync®
包尔星克



弯头电脑主机电源线

- 线材通过3C认证
- 标准国标三插90度头对品字尾
- 纯铜线芯，导电性好，RVV耐热线材安全实用
- PVC外被材质,韧度好,不易受外力拉扯断
- 原产地:中国上海

型号	长度/m	线材规格	外被线径/mm
MPPC0005	0.5	RVV 0.75mm ² x3C	6.7±0.2
MPPC0010	1.0	RVV 0.75mm ² x3C	6.7±0.2
MPPC0015	1.5	RVV 0.75mm ² x3C	6.7±0.2
MPPR0005	0.5	RVV 1.0mm ² x3C	7.0±0.2
MPPR0010	1.0	RVV 1.0mm ² x3C	7.0±0.2
MPPR0015	1.5	RVV 1.0mm ² x3C	7.0±0.2
MPPR0020	2.0	RVV 1.0mm ² x3C	7.0±0.2
MPPR0030	3.0	RVV 1.0mm ² x3C	7.0±0.2
MPPR0050	5.0	RVV 1.0mm ² x3C	7.0±0.2
MPPR0100	10	RVV 1.0mm ² x3C	7.0±0.2