


1	2	3	4	5	6	7	8
REVISION		DESCRIPTION		DATE	DRAFTER		
A1		FIRST RELEASED		20.07.21	Mark		



- 技术要求:
- 1 电气特性: 特性阻抗:50Ω; 适用频率范围:2.4GHz-2.5GHz; 驻波比:最大2.00。
检验方法: 使用矢量网络分析仪100%测试。
 - 2 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
 - 3 拔出力: 最小1.30kgf @ MHF-1-PLUG。
检验方法: 沿电缆中心轴, 以25±3毫米/分钟的速度, 垂直将1.30kg砝码提高离桌面即为合格, 反之不合格。
 - 3 外观要求: 产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
检验方法: 目视全检验。
 - 4 包装规范: 50PCS/扎, 10扎/包, 即500PCS/包。
 - 5 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

6	2TA040BK1-062	热缩套管, 单壁普通型, EVA, ∅4.0*L62, 黑色	1	---
5	2TA015BK1-015	热缩套管, 单壁普通型, EVA, ∅1.5*L15, 黑色	1	---
4	2YG022	信号柱, 黄铜, 表面除油	1	---
3	2YG013	接地管, 抽芯焊锡式, 铜镀锡	1	---
2	2LM10P113210	MHF-1 PLUG FOR OD1.13mm CABLE	1	---
1	2C5M11312BK1	微细同轴电缆, OD1.13mm, 双锡线, 黑色	1	依裁线图裁线
No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS

GENERAL TOLERANCE:
LINEAR:
X ±0.20
X.X ±0.15
X.XX ±0.05
X.XXX ±0.01
ANGLE:
X° ±4.00°
X.X° ±3.00°
X.XX° ±2.00°
X.XXX° ±1.00°

HJ-Tech 东莞市皇捷通讯科技有限公司

FILE NAME: 产品图 TITLE: 射频天线组件
ENG/DATE: Mark/20.07.21
CHE/DATE: P/N: HJ-IPEX1-RG1.13-380mm
APP/DATE: UNIT: mm SCALE: 1:1 REVISION: A0 SHEET: 1/1

COMPLIANCE WITH THE REQUIREMENT: ■ RoHS; □ HF; □ SONY SS-00259; □ OTHERS H514
*NO USING ESTRICTED AND BANNED SUBSTANCE