


**TOLERANCE:**

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				



	Dimension
<b>Ft±0.01</b>	0.043
<b>St±0.01</b>	0.225

**RoHS Compliant**

**UL Style : 20706**

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	
	FFCE0408T105000-300	04	0.5	1.5	50	2.5	0.5	0.3	0.05	4.0	4.0	8.0	8.0	BLUE

SYM	NAME	DATE	REVISIONS	APPROVED BY:	DATE	UNIT: mm	TITLE:					
4						TOLERANCE UNLESS OTHERWISE SPECIFIED	<b>FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)</b>	MATERIAL: SEE PRODUCT SPECIFICATION				
3				DRAWN BY: Lan	7/22-14							
2				ENGINEER: Lan	7/22-14			.x ±	x' ± 2'			
1				CHECKED BY: Lian	7/22-14			.xx ±	.x ±			
				APPROVED BY: Kenny	7/22-14	.xxx ±	.xx ±	CUST. CODE:	DRAWING NO. FFC001SF	FILE NO. T114257-4A	SCALE 1 / 1	SHEET 1 OF 1

**瀚荃股份有限公司**  
CviLux Corporation