


TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				

	Dimension
Ft±0.01	0.060
St±0.01	0.225



RoHS Compliant

UL Style : 20706 105C 60V Note:Gold Plated

Customer P/N	CviLux P/N	No. of Conductor	Dimension										Support Tape Color	
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1	S2±1	d1±2		d2±2
	FFCE0809Y1025AA-300	8	0.5	3.5	25	4.5	0.5	0.3	0.035	2	2	4	4	BLUE
	FFCE0809C1025AA-30R													
	FFCE0809Y1025AA-30R													
	FFCE0809Y1065AA-300	8	0.5	3.5	65	4.5	0.5	0.3	0.035	2	2	4	4	BLUE
	FFCE0809C1065AA-30R													
	FFCE0809Y1065AA-30R													

4		DATE	UNIT: mm	TITLE:	瀚荃股份有限公司 CviLux Corporation				
3		DRAWN BY: long	2/17-20'	FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)					
2		ENGINEER: long	2/17-20'	MATERIAL: SEE PRODUCT SPECIFICATION					
1		CHECKED BY: Kenny	2/17-20'	CUST. CODE:					
SYM	NAME	DATE	REVISIONS	APPROVED BY: Kenny	2/17-20'	DRAWING NO. FFC001SF	FILE NO. T119672-4A	SCALE 1 / 1	SHEET 1 OF 1