


**TOLERANCE:**

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				





Tolerance of Cutting Tilt

	Dimension
<b>Ft±0.01</b>	0.043
<b>St±0.01</b>	0.225

**RoHS Compliant**

**UL Style : 20706**

Customer P/N	CviLux P/N	No. of Conductor	Dimension										Support Tape Color	
			P	Pt	L	W	M	Cw	Ct±0.01	S1±0.5	S2±0.5	d1±1.0		d2±1.0
	FFCE2008T1050BA-300	20	0.5	9.5	50.0	10.5	0.5	0.3	0.05	2.5	2.5	4	4	BLUE
	FFCE2008T1060BA-300	20	0.5	9.5	60.0	10.5	0.5	0.3	0.05	2.5	2.5	4	4	

4					DATE	UNIT: mm	TITLE:	 瀚荃股份有限公司 CviLux Corporation					
3		DRAWN BY:	L an	8/10-16'	TOLERANCE UNLESS OTHERWISE SPECIFIED		<b>FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)</b>						
2		ENGINEER:	L an	8/10-16'	.x ±	X' ± 2'	MATERIAL: SEE PRODUCT SPECIFICATION						
1		CHECKED BY:	Kenny	8/10-16'	.xx ±	.x' ±	CUST. CODE:						
SYM		NAME	DATE	REVISIONS	APPROVED BY:	Kenny	8/10-16'	.xxx ±	.xx' ±	DRAWING NO.	FFC001SF	FILE NO.	T116231-4A
SCALE										1 / 1		SHEET 1 OF 1	