

TOLERANCE:


Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.20
Pt	±0.08	±0.10	±0.10	±0.15	+0.2 -0.4
W	±0.08	±0.10	±0.10	±0.20	+0.2 -0.4
M	±0.08	±0.15	±0.15	±0.20	±0.30
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				

	Dimension
Ft±0.01	0.043
St±0.01	0.225

UL Style : 20706

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	
	FFCE2008T108000-300	20	0.5	9.5	80	10.5	0.5	0.3	0.05	4	4	8	8	BLUE

RoHS Compliant



4	3	2	1	SYM	NAME	DATE	REVISIONS	APPROVED BY:	DATE	UNIT: mm	TITLE:	MATERIAL: SEE PRODUCT SPECIFICATION	DRAWING NO.	FILE NO.	CUST. CODE:	SCALE	SHEET	OF	1
											FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)								

瀚荃股份有限公司
CviLux Corporation