


Technical Parameters

- 1.Electrical Rating:0.1A 125/250VAC
0.1A/12VDC
- 2.Electrical lifetime:100 000
- 3.Mechanical lifetime:100 000
- 4.Contact Resistance: 50m
- 5.Operating force:1.5N MAX
- 6.FP:7.6mm MAX
- 7.OP:7.1 ± 0.3mm
- 8.TTP:5.1mm Min
- 9.Withstand Voltage:Feet and Feet 500V/5S/5mA
Feet and Shell 1500/5S/5mA
- 10.Insulation Resistance: 100M (Test Voltage 500VDC)
- 11.Proof Tracking Index(PTI):175V

Circuit diagram



Waterproof grade:IP67

1	Rubber shell	PA66
2	seal ring	Silica gel
3	base	Brass+PA66
4	According to sincerity	POM
5	Contact moving plate	C5191+AgNi10
6	Strut	SUS301-H

					DSND		DATE		SCALE: N/A	MODEL TYPE: Microswitch		
					ANGLAR		DATE		VIEW:	PART NO.:		
ΔX					L ≤ 4	±0.2	DATE		UNIT: mm	DWG NO.: DF1-CZ-3		
ΔX					4 < L ≤ 16	±0.3	DATE		SIZE: A4			
ΔX					16 < L ≤ 63	±0.4	DATE					
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5	DATE					
REVISIONS					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn										1.0g	1/1	A0